
# DATA SHEET



### 790MM ACTIVESMART<sup>™</sup> FRIDGE

#### RF170BLPW6, RF170BLPX6, RF170BLZX6, RF170BLZW6

(refer page 2 for metric measurements)


Product Dimensions	in
Overall height* of fridge	67 3/4"
Overall width of fridge	31 1/8"
© Depth of fridge door and gasket	2 3/4"
<ul> <li>Depth of fridge door and chassis</li> </ul>	27 3/8"
E Depth of fridge chassis (does not include fridge door)	24 5/8"
Height of feet (adjustable)	15/16″
© Height from bottom of chassis to bottom of bottom door	5/8"
Height from bottom of chassis to top of bottom door	24 5/8"
③ Gap between doors	3/8"
Height of top door	41 3/4"
© Depth of door gasket	9/16″
© Depth of evaporator tray	1 3/16"
O Depth of door (open at 90°) (measured from front of door)	29 5/16"
Rotation of door (open)	138°

Minimum Clearances	in
Minimum height of cavity	68 5/16"
Minimum side clearance installed flush with chassis	13/16″
Side clearance (hinge side) installed flush with door - full rotation	5 5/16"
Rear clearance (including evaporator tray)	1 3/16″

INDICATES PRODUCT DATUM ---INDICATES CABINETRY CLEARANCES ------

IMPORTANT NOTE: Throughout this guide, dimensions may vary by  $\pm 2mm$ (3/32"). Please read the installation manual for detailed information on installing the product. www.fisherpaykel.com

# DATA SHEET



### 790MM ACTIVESMART<sup>™</sup> FRIDGE

#### RF170BLPW6, RF170BLPX6, RF170BLZX6, RF170BLZW6

(refer page 1 for imperial measurements)

Product Dimensions	mm
<ul> <li>Overall height* of fridge</li> </ul>	1720
Overall width of fridge	790
© Depth of fridge door and gasket	70
Depth of fridge door and chassis	695
© Depth of fridge chassis (does not include fridge door)	625
F Height of feet (adjustable)	24
G Height from bottom of chassis to bottom of bottom door	16
Height from bottom of chassis to top of bottom door	626
① Gap between doors	10
Height of top door	1060
Depth of door gasket	15
Depth of evaporator tray	30
Depth of door (open at 90°) (measured from front of door)	745
Rotation of door (open)	138°

Minimum Clearances	mm
Minimum height of cavity	1735
Minimum side clearance installed flush with chassis	20
Side clearance (hinge side) installed flush with door - full rotation	135
Rear clearance (including evaporator tray)	30

INDICATES CABINETRY CLEARANCES ------

IMPORTANT NOTE: Throughout this guide, dimensions may vary by  $\pm 2mm$ (3/32"). Please read the installation manual for detailed information on installing the product. www.fisherpaykel.com